

FOCAL LENGTH (EFL): $8 \pm 0,08$
 BACK FOCAL LENGTH (BFL): 7,17

1 AR COATING: NONE

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	5,36±0,005 CX	GLASS N-BaF10 670/472	R	∞ PL
Øe	3,6		Øe	3,6
3/	3 (0,5) $\lambda=632,8$ nm		3/	3 (0,5) $\lambda=632,8$ nm
4/	-		4/	4,48'
5/	20 - 10 (MIL-PRF-13830B)		5/	20 - 10 (MIL-PRF-13830B)
6/	-		6/	-

PROTECTIVE CHAMFERS AS NEEDED


ROHS: COMPLIANT
 SCALE: NONE
 $\lambda = 587,6$ nm

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

INDICATIONS IN ACCORDANCE WITH ISO 10110

FIRST ANGLE PROJECTION



ALL DIMS IN: mm

EO® Edmund Optics®

TITLE 4,0mm Dia, x 8,0mm FL, Uncoated, Plano-Convex Lens

DWG NO 45225

SHEET SIZE A4 SHEET 1 OF 1