



FOCAL LENGTH (EFL): 85 ± 0,85
 BACK FOCAL LENGTH (BFL): 82,17

- 1 AR COATING: VIS-NIR
 R(ABS) ≤ 0,25% AT 880nm @ 0° AOI
 R(AVG) ≤ 1,25% FROM 400-870nm @ 0° AOI
 R(AVG) ≤ 1,25% FROM 890-1000nm @ 0° AOI
- 2 BLACKENED SURFACE

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	43,93±0,044 CX	GLASS N-BK7 517/642	R	∞ PL
Øe	24		Øe	24
3/	3 (0,5) λ=632,8 nm		3/	3 (0,5) λ=632,8 nm
4/	-		4/	1,93'
5/	40 - 20 (MIL-PRF-13830B)		5/	40 - 20 (MIL-PRF-13830B)
6/	-		6/	-

PROTECTIVE CHAMFERS AS NEEDED			FIRST ANGLE PROJECTION				
ROHS: COMPLIANT	SCALE: NONE	λ = 587,6nm					
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY				TITLE	25,0mm Dia, x 85,0mm FL, VIS-NIR, Inked, Plano-Convex Lens		
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING				ALL DIMS IN:	DWG NO	45511INK	SHEET SIZE
INDICATIONS IN ACCORDANCE WITH ISO 10110						SHEET	1 OF 1