




FOCAL LENGTH (EFL): $15 \pm 0,15$

BACK FOCAL LENGTH (BFL): 13,262

- 1 AR COATING: YAG-BBAR
 $R(ABS) < 0,25\% @ 532nm @ 0^\circ AOI$
 $R(ABS) < 0,25\% @ 1064nm @ 0^\circ AOI$
 $R(AVG) < 1,0\% FROM 500-1100nm @ 0^\circ AOI$

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	11,77±0,012 CX	GLASS N-SF11 785/258	R	∞ PL
Øe	11,5		Øe	11,5
3/	3 (0,5) $\lambda=632,8$ nm		3/	3 (0,5) $\lambda=632,8$ nm
4/	-		4/	1,27'
5/	40 - 20 (MIL-PRF-13830B)		5/	40 - 20 (MIL-PRF-13830B)
6/	-		6/	-

PROTECTIVE CHAMFERS AS NEEDED


ROHS: COMPLIANT SCALE: NONE $\lambda = 587,6nm$

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

INDICATIONS IN ACCORDANCE WITH ISO 10110

FIRST ANGLE PROJECTION



ALL DIMS IN: mm



Edmund Optics®

TITLE 12,5mm Dia, x 15,0mm FL, YAG-BBAR Coated, Plano-Convex Lens

DWG NO 38579

SHEET SIZE A4

SHEET 1 OF 1