



FOCAL LENGTH (EFL): 15 ±0,15
 BACK FOCAL LENGTH (BFL): 13,68

1 AR COATING: NONE

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	22,51±0,023 CX	GLASS N-SF11 785/258	R	22,51±0,023 CX
Øe	14		Øe	14
3/	3 (0,5) λ=632,8 nm		3/	3 (0,5) λ=632,8 nm
4/	-		4/	1,27'
5/	40 - 20 (MIL-PRF-13830B)		5/	40 - 20 (MIL-PRF-13830B)
6/	-		6/	-

PROTECTIVE CHAMFERS AS NEEDED

ROHS: COMPLIANT
 SCALE: NONE λ = 587,6nm

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

INDICATIONS IN ACCORDANCE WITH ISO 10110

FIRST ANGLE PROJECTION



ALL DIMS IN: mm

EO® Edmund Optics®

TITLE 15mm Dia, x 15mm FL Uncoated, Double-Convex Lens

DWG NO 45099

SHEET SIZE A4 SHEET 1 OF 1