



FOCAL LENGTH (EFL):  $-6 \pm 0,06$   
 BACK FOCAL LENGTH (BFL):  $-6,41$

- 1 AR COATING: VIS  $0^\circ$   
 $R(\text{AVG}) \leq 0,4\%$  FROM 425-675nm @  $0^\circ$  AOI
- 2 BLACKENED SURFACE

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	9,74±0,01 CV	GLASS N-SF11 785/258	R	9,74±0,01 CV
Øe	5,4		Øe	5,4
3/	3 (0,5) $\lambda=632,8$ nm		3/	3 (0,5) $\lambda=632,8$ nm
4/	-		4/	3,82'
5/	40 - 20 (MIL-PRF-13830B)		5/	40 - 20 (MIL-PRF-13830B)
6/	-		6/	-

PROTECTIVE CHAMFERS AS NEEDED

ROHS: COMPLIANT    SCALE: NONE     $\lambda = 587,6\text{nm}$

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

INDICATIONS IN ACCORDANCE WITH ISO 10110

FIRST ANGLE PROJECTION



ALL DIMS IN: mm

**EO**® Edmund Optics®

TITLE 6mm Dia, x -6mm FL, VIS 0, Inked, Double-Concave Lens

DWG NO 479141NK

SHEET SIZE A4    SHEET 1 OF 1