

FOCAL LENGTH (EFL):  $9 \pm 0,09$   
 BACK FOCAL LENGTH (BFL): 7,41

1 AR COATING: NONE

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	4,65±0,005 CX	GLASS N-BK7 517/642	R	$\infty$ PL
Øe	4,05		Øe	4,05
3/	3 (0,5) $\lambda=632,8$ nm		3/	3 (0,5) $\lambda=632,8$ nm
4/	-		4/	5,8'
5/	40 - 20 (MIL-PRF-13830B)		5/	40 - 20 (MIL-PRF-13830B)
6/	-		6/	-

PROTECTIVE CHAMFERS AS NEEDED


ROHS: COMPLIANT    SCALE: NONE     $\lambda = 587,6$ nm

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

INDICATIONS IN ACCORDANCE WITH ISO 10110

FIRST ANGLE PROJECTION



ALL DIMS IN: mm

**EO**® Edmund Optics®

TITLE 4,5mm Dia, x 9,0mm FL, Uncoated, Plano-Convex Lens

DWG NO 45147

SHEET SIZE A4 SHEET 1 OF 1