



FOCAL LENGTH (EFL): $75 \pm 0,75$
 BACK FOCAL LENGTH (BFL): 74,11

- 1 AR COATING: UV-AR
 $R(\text{ABS}) \leq 1,0\%$ FROM 250-425nm @ 0° AOI
 $R(\text{AVG}) \leq 0,75\%$ FROM 250-425nm @ 0° AOI
 $R(\text{AVG}) \leq 0,5\%$ FROM 370-420nm @ 0° AOI

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	68,362±0,068 CX	GLASS FUSED SILICA 458/678	R	68,362±0,068 CX
Øe	11		Øe	11
3/	3 (0,5) $\lambda=632,8$ nm		3/	3 (0,5) $\lambda=632,8$ nm
4/	-		4/	2,18'
5/	40 - 20 (MIL-PRF-13830B)		5/	40 - 20 (MIL-PRF-13830B)
6/	-		6/	-

PROTECTIVE CHAMFERS AS NEEDED

ROHS: COMPLIANT
 SCALE: NONE $\lambda = 587,6\text{nm}$

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

INDICATIONS IN ACCORDANCE WITH ISO 10110

FIRST ANGLE PROJECTION



ALL DIMS IN: mm

EO® Edmund Optics®

TITLE 12mm Dia, x 75mm FL, UV-AR Coated, UV Double-Convex Lens

DWG NO 48045

SHEET SIZE A4
 SHEET 1 OF 1