



FOCAL LENGTH (EFL):  $-6 \pm 0,06$   
 BACK FOCAL LENGTH (BFL):  $-6,84$

1 AR COATING: VIS  $0^\circ$   
 $R(\text{AVG}) \leq 0,4\%$  FROM 425-675nm @  $0^\circ$  AOI

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	$4,71 \pm 0,005$ CV	GLASS N-SF11 785/258	R	$\infty$ PL
Øe	5,4		Øe	5,4
3/	3 (0,5) $\lambda=632,8$ nm		3/	3 (0,5) $\lambda=632,8$ nm
4/	-		4/	3,82'
5/	40 - 20 (MIL-PRF-13830B)		5/	40 - 20 (MIL-PRF-13830B)
6/	-		6/	-

PROTECTIVE CHAMFERS AS NEEDED

ROHS: COMPLIANT  
 SCALE: NONE  
 $\lambda = 587,6$ nm

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

INDICATIONS IN ACCORDANCE WITH ISO 10110

FIRST ANGLE PROJECTION



ALL DIMS IN: mm



Edmund Optics®

TITLE 6mm Diameter x -6 FL, VIS 0 Coated, Plano-Concave Lens

DWG NO 48265

SHEET SIZE A4  
 SHEET 1 OF 1