



FOCAL LENGTH (EFL): 27 ±0,27
 BACK FOCAL LENGTH (BFL): 25,63

- 1 AR COATING: UV-AR
 R(ABS) ≤ 1,0% FROM 250-425nm @ 0° AOI
 R(AVG) ≤ 0,75% FROM 250-425nm @ 0° AOI
 R(AVG) ≤ 0,5% FROM 370-420nm @ 0° AOI

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	12,38±0,012 CX	GLASS FUSED SILICA 458/678	R	∞ PL
Øe	8,1		Øe	8,1
3/	3 (0,5) λ=632,8 nm		3/	3 (0,5) λ=632,8 nm
4/	-		4/	2,18'
5/	40 - 20 (MIL-PRF-13830B)		5/	40 - 20 (MIL-PRF-13830B)
6/	-		6/	-

PROTECTIVE CHAMFERS AS NEEDED		FIRST ANGLE PROJECTION		
ROHS: COMPLIANT	SCALE: NONE			
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY			TITLE	
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING			9mm Dia, x 27mm FL UV-AR Coated, UV Plano-Convex Lens	
INDICATIONS IN ACCORDANCE WITH ISO 10110		ALL DIMS IN: mm	DWG NO	46260
			SHEET SIZE	A4
			SHEET	1 OF 1