



FOCAL LENGTH (EFL): 250 ±2,5
 BACK FOCAL LENGTH (BFL): 248,9

1 AR COATING: UV-VIS
 R(AVG) ≤ 1,5% FROM 250-700nm @ 0° AOI
 R(ABS) ≤ 1,0% FROM 350-450nm @ 0° AOI

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	228,725±0,229 CX	GLASS FUSED SILICA 458/678	R	228,725±0,229 CX
Øe	24		Øe	24
3/	3 (0,5) λ=632,8 nm		3/	3 (0,5) λ=632,8 nm
4/	-		4/	2,18'
5/	40 - 20 (MIL-PRF-13830B)		5/	40 - 20 (MIL-PRF-13830B)
6/	-		6/	-

PROTECTIVE CHAMFERS AS NEEDED		FIRST ANGLE PROJECTION			
ROHS: COMPLIANT	SCALE: NONE λ = 587,6nm				
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY			TITLE	25mm Dia, x 250mm, UV-VIS Coated, UV Double-Convex Lens	
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING			ALL DIMS IN: mm	DWG NO	48850
INDICATIONS IN ACCORDANCE WITH ISO 10110					SHEET 1 OF 1