



FOCAL LENGTH (EFL): 300 ± 3
 BACK FOCAL LENGTH (BFL): 298,94

- 1 AR COATING: UV-AR
 $R(\text{ABS}) \leq 1,0\%$ FROM 250-425nm @ 0° AOI
 $R(\text{AVG}) \leq 0,75\%$ FROM 250-425nm @ 0° AOI
 $R(\text{AVG}) \leq 0,5\%$ FROM 370-420nm @ 0° AOI

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	274,601±0,275 CX	GLASS FUSED SILICA 458/678	R	274,601±0,275 CX
Øe	24		Øe	24
3/	3 (0,5) $\lambda=632,8$ nm		3/	3 (0,5) $\lambda=632,8$ nm
4/	-		4/	2,18'
5/	40 - 20 (MIL-PRF-13830B)		5/	40 - 20 (MIL-PRF-13830B)
6/	-		6/	-

PROTECTIVE CHAMFERS AS NEEDED		FIRST ANGLE PROJECTION				
ROHS: COMPLIANT	SCALE: NONE $\lambda = 587,6\text{nm}$					
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY			TITLE	25mm Dia, x 300mm FL, UV-AR Coated, UV Double-Convex Lens		
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING			ALL DIMS IN:	mm	DWG NO	
INDICATIONS IN ACCORDANCE WITH ISO 10110				48313	SHEET SIZE A4	SHEET 1 OF 1