



FOCAL LENGTH (EFL): $18 \pm 0,18$
 BACK FOCAL LENGTH (BFL): 17,3

1 AR COATING: NONE

| LEFT SURFACE | | MATERIAL | RIGHT SURFACE | |
|--------------|----------------------------|----------------------------|---------------|----------------------------|
| R | 16,18±0,016 CX | GLASS FUSED SILICA 458/678 | R | 16,18±0,016 CX |
| Øe | 5,4 | | Øe | 5,4 |
| 3/ | 3 (0,5) $\lambda=632,8$ nm | | 3/ | 3 (0,5) $\lambda=632,8$ nm |
| 4/ | - | | 4/ | 2,18' |
| 5/ | 40 - 20 (MIL-PRF-13830B) | | 5/ | 40 - 20 (MIL-PRF-13830B) |
| 6/ | - | | 6/ | - |

| | | | | | |
|--|----------------------------------|---|--|---|--------------|
| PROTECTIVE CHAMFERS AS NEEDED | | FIRST ANGLE PROJECTION |  | | |
| ROHS: COMPLIANT | SCALE: NONE $\lambda = 587,6$ nm | | | | |
| SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY | |  | TITLE | 6mm Dia, x 18mm FL, Uncoated, UV Double-Convex Lens | |
| FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING | | | ALL DIMS IN: | mm | DWG NO |
| INDICATIONS IN ACCORDANCE WITH ISO 10110 | | | | SHEET SIZE | A4 |
| | | | | | SHEET 1 OF 1 |