



FOCAL LENGTH (EFL):  $30 \pm 0,3$   
 BACK FOCAL LENGTH (BFL): 26,13

1 AR COATING: VIS  $0^\circ$   
 $R(\text{AVG}) \leq 0,4\%$  FROM 425-675nm @  $0^\circ$  AOI

| LEFT SURFACE |                            | MATERIAL             | RIGHT SURFACE |                            |
|--------------|----------------------------|----------------------|---------------|----------------------------|
| R            | 23,541±0,024 CX            | GLASS N-SF11 785/258 | R             | $\infty$ PL                |
| Øe           | 29                         |                      | Øe            | 29                         |
| 3/           | 3 (0,5) $\lambda=632,8$ nm |                      | 3/            | 3 (0,5) $\lambda=632,8$ nm |
| 4/           | -                          |                      | 4/            | 1,27'                      |
| 5/           | 40 - 20 (MIL-PRF-13830B)   |                      | 5/            | 40 - 20 (MIL-PRF-13830B)   |
| 6/           | -                          |                      | 6/            | -                          |

PROTECTIVE CHAMFERS AS NEEDED

ROHS: COMPLIANT  
 SCALE: NONE  
 $\lambda = 587,6$ nm

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

INDICATIONS IN ACCORDANCE WITH ISO 10110

FIRST ANGLE PROJECTION



ALL DIMS IN: mm

**EO**® Edmund Optics®

TITLE 30,0mm Dia, x 30,0mm FL, VIS 0 Coated, Plano-Convex Lens

DWG NO 48659

SHEET SIZE A4 SHEET 1 OF 1