



FOCAL LENGTH (EFL): 20 ±0,2
 BACK FOCAL LENGTH (BFL): 17,74

1 AR COATING:
 ¼ WAVE MgF2 @ 550nm
 R(AVG) < 1,75% FROM 400-700nm (N-BK7)

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	13,46±0,013 CX	GLASS N-SF5 673/322	R	∞ PL
Øe	14		Øe	14
3/	3 (0,5) λ=632,8 nm		3/	3 (0,5) λ=632,8 nm
4/	-		4/	1,49'
5/	40 - 20 (MIL-PRF-13830B)		5/	40 - 20 (MIL-PRF-13830B)
6/	-		6/	-

PROTECTIVE CHAMFERS AS NEEDED			FIRST ANGLE PROJECTION				
ROHS: COMPLIANT	SCALE: NONE	λ = 587,6nm					
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY				TITLE 15,0mm Dia, x 20,0mm FL, MgF2 Coated, Plano-Convex Lens			
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING				ALL DIMS IN: mm	DWG NO 63493	SHEET SIZE A4	SHEET 1 OF 1
INDICATIONS IN ACCORDANCE WITH ISO 10110							