

FOCAL LENGTH (EFL):  $20 \pm 0,2$

BACK FOCAL LENGTH (BFL): 17,74

- 1 AR COATING: VIS  $0^\circ$   
R(AVG)  $\leq 0,4\%$  FROM 425-675nm @  $0^\circ$  AOI
- 2 BLACKENED SURFACE

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	13,46 $\pm$ 0,013 CX	GLASS N-SF5 673/322	R	$\infty$ PL
$\text{\O}e$	14		$\text{\O}e$	14
3/	3 (0,5) $\lambda=632,8$ nm		3/	3 (0,5) $\lambda=632,8$ nm
4/	-		4/	1,49'
5/	40 - 20 (MIL-PRF-13830B)		5/	40 - 20 (MIL-PRF-13830B)
6/	-		6/	-

PROTECTIVE CHAMFERS AS NEEDED


ROHS: COMPLIANT  
SCALE: NONE  
 $\lambda = 587,6$ nm

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

INDICATIONS IN ACCORDANCE WITH ISO 10110

FIRST ANGLE PROJECTION



ALL DIMS IN: mm

**EO**® Edmund Optics®

TITLE 15,0mm Dia, x 20,0mm FL, VIS 0, Inked, Plano-Convex Lens

DWG NO 635061NK

SHEET SIZE A4  
SHEET 1 OF 1