



FOCAL LENGTH (EFL): 40 ±0,4
 BACK FOCAL LENGTH (BFL): 36,77

1 AR COATING: NIR I
 R(AVG) ≤ 0,5% FROM 600-1050nm @ 0° AOI

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	20,67±0,021 CX	GLASS N-BK7 517/642	R	∞ PL
Øe	19		Øe	19
3/	3 (0,5) λ=632,8 nm		3/	3 (0,5) λ=632,8 nm
4/	-		4/	1,93'
5/	40 - 20 (MIL-PRF-13830B)		5/	40 - 20 (MIL-PRF-13830B)
6/	-		6/	-

PROTECTIVE CHAMFERS AS NEEDED		FIRST ANGLE PROJECTION						
ROHS: COMPLIANT	SCALE: NONE				λ = 587,6nm			
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY			TITLE 20,0mm Dia, x 40,0mm FL, NIR I Coated, Plano-Convex Lens					
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING								
INDICATIONS IN ACCORDANCE WITH ISO 10110		ALL DIMS IN: mm	DWG NO	48759	SHEET SIZE	A4	SHEET	1 OF 1