



FOCAL LENGTH (EFL):  $80 \pm 0,8$   
 BACK FOCAL LENGTH (BFL):  $77,33$

1 AR COATING: NIR I  
 $R(AVG) \leq 0,5\%$  FROM 600-1050nm @  $0^\circ$  AOI

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	$82,29 \pm 0,082$ CX	GLASS N-K5 523/595	R	$82,29 \pm 0,082$ CX
$\varnothing e$	39		$\varnothing e$	39
3/	3 (0,5) $\lambda=632,8$ nm		3/	3 (0,5) $\lambda=632,8$ nm
4/	-		4/	1,91'
5/	40 - 20 (MIL-PRF-13830B)		5/	40 - 20 (MIL-PRF-13830B)
6/	-		6/	-

PROTECTIVE CHAMFERS AS NEEDED		FIRST ANGLE PROJECTION	<b>Edmund Optics®</b>		
ROHS: COMPLIANT	SCALE: NONE $\lambda = 587,6$ nm				
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY			TITLE	40mm Dia, x 80mm FL, NIR I Coated, DCX N-K5 Lens	
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING			ALL DIMS IN: mm	DWG NO	49504
INDICATIONS IN ACCORDANCE WITH ISO 10110					SHEET 1 OF 1