



FOCAL LENGTH (EFL): $12 \pm 0,12$
 BACK FOCAL LENGTH (BFL): $10,6$

- 1 AR COATING: NIR II
 $R(\text{ABS}) \leq 1,5\%$ FROM 750-800nm @ 0° AOI
 $R(\text{ABS}) \leq 1,0\%$ FROM 800-1550nm @ 0° AOI
 $R(\text{AVG}) \leq 0,7\%$ FROM 750-1550nm @ 0° AOI
- 2 BLACKENED SURFACE

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	$9,42 \pm 0,009$ CX	GLASS N-SF11 785/258	R	∞ PL
Øe	8,1		Øe	8,1
3/	3 (0,5) $\lambda=632,8$ nm		3/	3 (0,5) $\lambda=632,8$ nm
4/	-		4/	1,27'
5/	40 - 20 (MIL-PRF-13830B)		5/	40 - 20 (MIL-PRF-13830B)
6/	-		6/	-

PROTECTIVE CHAMFERS AS NEEDED

ROHS: COMPLIANT
 SCALE: NONE
 $\lambda = 587,6$ nm

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

INDICATIONS IN ACCORDANCE WITH ISO 10110

FIRST ANGLE PROJECTION



ALL DIMS IN: mm

EO® Edmund Optics®

TITLE 9,0mm Dia, x 12,0mm FL, NIR II, Inked, Plano-Convex Lens

DWG NO 674731NK

SHEET SIZE A4
 SHEET 1 OF 1