

FOCAL LENGTH (EFL): $50,8 \pm 0,51$
 BACK FOCAL LENGTH (BFL): 47,5

- 1 AR COATING: NIR II
 $R(\text{ABS}) \leq 1,5\%$ FROM 750-800nm @ 0° AOI
 $R(\text{ABS}) \leq 1,0\%$ FROM 800-1550nm @ 0° AOI
 $R(\text{AVG}) \leq 0,7\%$ FROM 750-1550nm @ 0° AOI

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	26,25±0,026 CX	GLASS N-BK7 517/642	R	∞ PL
Øe	24,4		Øe	24,4
3/	3 (0,5) λ=632,8 nm		3/	3 (0,5) λ=632,8 nm
4/	-		4/	1,93'
5/	40 - 20 (MIL-PRF-13830B)		5/	40 - 20 (MIL-PRF-13830B)
6/	-		6/	-

PROTECTIVE CHAMFERS AS NEEDED


ROHS: COMPLIANT
 SCALE: NONE
 $\lambda = 587,6\text{nm}$

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

INDICATIONS IN ACCORDANCE WITH ISO 10110

FIRST ANGLE PROJECTION



ALL DIMS IN: mm



Edmund Optics®

TITLE 25,4mm Dia, x 50,8mm FL, NIR II Coated, Plano-Convex Lens

DWG NO 67562

SHEET SIZE A4

SHEET 1 OF 1