



FOCAL LENGTH (EFL): $175 \pm 1,75$

BACK FOCAL LENGTH (BFL): $172,85$

1 AR COATING: 980nm V-COAT
 $R(\text{ABS}) < 0,25\% @ 980\text{nm} @ 0^\circ \text{AOI}$

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	$90,47 \pm 0,09 \text{ CX}$	GLASS N-BK7 517/642	R	$\infty \text{ PL}$
Øe	24		Øe	24
3/	3 (0,5) $\lambda=632,8 \text{ nm}$		3/	3 (0,5) $\lambda=632,8 \text{ nm}$
4/	-		4/	1,93'
5/	40 - 20 (MIL-PRF-13830B)		5/	40 - 20 (MIL-PRF-13830B)
6/	-		6/	-

PROTECTIVE CHAMFERS AS NEEDED

ROHS: COMPLIANT SCALE: NONE $\lambda = 587,6\text{nm}$

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

INDICATIONS IN ACCORDANCE WITH ISO 10110

FIRST ANGLE PROJECTION



ALL DIMS IN: mm

EO® Edmund Optics®

TITLE 25,0mm Diameter x 175,0mm FL, 980nm V-Coat, PCX Lens

DWG NO 69573

SHEET SIZE A4 SHEET 1 OF 1