



FOCAL LENGTH (EFL):  $60 \pm 0,6$

BACK FOCAL LENGTH (BFL):  $56,9$

1 AR COATING: 1310nm V-COAT  
 R(ABS) < 0,25% @ 1310nm @ 0° AOI

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	$31,01 \pm 0,031$ CX	GLASS N-BK7 517/642	R	$\infty$ PL
$\varnothing e$	24		$\varnothing e$	24
3/	3 (0,5) $\lambda=632,8$ nm		3/	3 (0,5) $\lambda=632,8$ nm
4/	-		4/	1,93'
5/	40 - 20 (MIL-PRF-13830B)		5/	40 - 20 (MIL-PRF-13830B)
6/	-		6/	-

PROTECTIVE CHAMFERS AS NEEDED

ROHS: COMPLIANT  
 SCALE: NONE  
 $\lambda = 587,6$ nm

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

INDICATIONS IN ACCORDANCE WITH ISO 10110

FIRST ANGLE PROJECTION



ALL DIMS IN: mm

**EO**® Edmund Optics®

TITLE 25,0mm Diameter x 60,0mm FL, 1310nm V-Coat, PCX Lens

DWG NO 84185

SHEET SIZE A4 SHEET 1 OF 1