



FOCAL LENGTH (EFL): $5 \pm 0,05$
 BACK FOCAL LENGTH (BFL): 4,19

1 AR COATING: NONE

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	6,18±0,006 CX	GLASS N-SF5 673/322	R	6,18±0,006 CX
Øe	4,5		Øe	4,5
3/	3 (0,5) $\lambda=632,8$ nm		3/	3 (0,5) $\lambda=632,8$ nm
4/	-		4/	66,86'
5/	40 - 20 (MIL-PRF-13830B)		5/	40 - 20 (MIL-PRF-13830B)
6/	-		6/	-

PROTECTIVE CHAMFERS AS NEEDED

ROHS: COMPLIANT SCALE: NONE $\lambda = 587,6$ nm

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

INDICATIONS IN ACCORDANCE WITH ISO 10110

FIRST ANGLE PROJECTION



ALL DIMS IN: mm

EO® Edmund Optics®

TITLE 5mm Dia, x 5mm FL, Uncoated, Double-Convex Lens

DWG NO 63530

SHEET SIZE A4 SHEET 1 OF 1