



FOCAL LENGTH (EFL): $40 \pm 0,4$
 BACK FOCAL LENGTH (BFL): $36,77$

1 AR COATING: 532nm V-COAT
 $R(\text{ABS}) < 0,25\% @ 532\text{nm} @ 0^\circ \text{AOI}$

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	$20,67 \pm 0,021 \text{ CX}$	GLASS N-BK7 517/642	R	$\infty \text{ PL}$
$\varnothing e$	19		$\varnothing e$	19
3/	3 (0,5) $\lambda=632,8 \text{ nm}$		3/	3 (0,5) $\lambda=632,8 \text{ nm}$
4/	-		4/	1,93'
5/	40 - 20 (MIL-PRF-13830B)		5/	40 - 20 (MIL-PRF-13830B)
6/	-		6/	-

PROTECTIVE CHAMFERS AS NEEDED		FIRST ANGLE PROJECTION			
ROHS: COMPLIANT	SCALE: NONE				
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY			TITLE	20,0mm Diameter x 40,0mm FL, 532nm V-Coat, PCX Lens	
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING			DWG NO	88990	SHEET SIZE A4
INDICATIONS IN ACCORDANCE WITH ISO 10110			ALL DIMS IN:	mm	SHEET 1 OF 1