


NOTES:

1. SUBSTRATE: POLYMER FILM XP44-40
2. OPERATING TEMPERATURE: -40 to +80 °C
3. WAVELENGTH RANGE: 400 - 700nm
4. EXTINCTION RATIO: 2,000:1
5. POLARIZATION EFFICIENCY (%): >99.95
6. TRANSMISSION (%):  
 SINGLE:  $44.2 \pm 1.5$   
 PARALLEL: 38.6  
 CROSSED: <0.02
7. ROHS COMPLIANT



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
 DIMENSIONS ARE FOR REFERENCE ONLY



**FOR INFORMATION ONLY:  
 DO NOT MANUFACTURE  
 PARTS TO THIS DRAWING**

THIRD ANGLE PROJECTION		TITLE	250 x 250mm HIGH TRANSMISSION LINEAR POLARIZING FILM (XP44-40)	
ALL DIMS IN	mm	DWG NO	14353	SHEET 1 OF 1