


NOTES:


- 1. SUBSTRATE: POLYMER FILM XP44-40
- 2. OPERATING TEMPERATURE: -40 TO +80 °C
- 3. WAVELENGTH RANGE: 400 - 700 nm
- 4. EXTINCTION RATIO: 2000:1
- 5. POLARIZATION EFFICIENCY (%): >99.95
- 6. TRANSMISSION (%):  
SINGLE: 44.2 ±1.5  
PARALLEL: 38.6  
CROSSED: <0.02
- 7. ROHS COMPLIANT



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

**EO**® Edmund Optics®

THIRD ANGLE PROJECTION 		TITLE	150 x 150mm High Transmission Linear Polarizing Film (XP44-40)	
ALL DIMS IN	mm	DWG NO	19021	SHEET 1 OF 1