




705 St. Paul Street
 Rochester, New York 14605
 Telephone: (585) 248-4100
 Fax: (585) 248-4111
 E-mail: gratings@newport.com
 Web Site: <https://www.gratinglab.com>

DIFFRACTION GRATING SPECIFICATION SHEET

Catalog no.	53-*-260R	12/23/2024
Grating Description	600 g/mm plane ruled reflection grating with 8.6° nominal blaze angle	
Master no.	1267	
Maximum Ruled Area:		groove length: 154 mm
		ruled width: 206 mm

Efficiency Curve	spectral order:	m = 1	polarization(s):	S and P
	Coating:	aluminum		
Remarks:				



Note: The efficiency curve above is relative (not absolute) and was measured in an in-plane near Littrow configuration (unless otherwise indicated). Efficiency curves are only representative: actual efficiency may vary significantly depending on use geometry and measurement technique. This efficiency curve is for master 1267; two masters with the same catalog number may have different efficiency curves. The uncertainty band on the data in the above efficiency curve(s) is +/- three percentage points.

©2024 Newport Corporation All rights reserved.