

[All Products](#) / [Lasers](#) / [Laser Sources](#) / [Industrial and Pointing Lasers](#)

Micro LDM Laser Diode Modules



- 7mm Housing Diameter
- Focusable
- Low Voltage DC Operation
- Reverse Polarity Protection



Common Specifications

Note:	Includes: Users Manual, Warning Label, and Focus Key	Type of Laser:	Diode
Weight (g):	3	Length of Leads (mm):	220
Length (mm):	27.40		
Beam Divergence (mrad):			<0.5
Focus Range (mm):			50mm - ∞
Output Power Tolerance (%):			±5 at 25°C
Electrical Leads/ Pin Connections:	red (+), black (-)	Output Type:	Free Space
Operating Temperature (°C):	-10 to +45	Storage Temperature (°C):	-10 to +85

Technical Information

Products

Wavelength (nm)	Output Power (mW)	Beam Size at Nearest Focus (μm)	Beam Diameter (mm)	Beam Divergence (mrad)	Stock Number	Price	Buy
635.00	0.9	<40	3 x 1	<0.5	#57-098	\$158.00 Volume Pricing	14 In Stock
655.00	0.9	<40	3 x 1	<0.5	#57-100	\$158.00 Volume Pricing	3 In Stock
515.00	1	<40	3 x 1 at Aperture	<0.5	#72-824	\$252.00 Volume Pricing	Contact Us
635.00	3	<40	3 x 1	<0.5	#57-099	\$158.00 Volume Pricing	9 In Stock
655.00	3	<40	3 x 1	<0.5	#57-101	\$158.00 Volume Pricing	3 In Stock
515.00	5	<40	3 x 1 at Aperture	<0.5	#72-825	\$263.00 Volume Pricing	1 In Stock



Copyright 2023, Edmund Optics Inc., 101 East Gloucester Pike, Barrington, NJ 08007-1380 USA

Phone: 1-800-363-1992 :

www.edmundoptics.com