

TECHSPEC<sup>®</sup> 20 x 20mm Protected Gold, 4-6λ Mirror



Stock #43-883 ☐ In Stock

-

1

+

\$45.00

ADD TO CART

|                               |
|-------------------------------|
| Qty 1-5                       |
| \$45.00                       |
| Qty 6+                        |
| \$34.00                       |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

Get Product Downloads

Surface Flatness (P-V):  
4 - 6λ

Substrate: ☐  
Float Glass

Surface Quality:  
60-40

Dimensions (mm):  
20.0 x 20.0

|                                                                                                                  |
|------------------------------------------------------------------------------------------------------------------|
| <b>Dimensional Tolerance (mm):</b><br>±0.25                                                                      |
| <b>Coating Specification:</b><br>R <sub>avg</sub> >96% @ 700 - 2000nm<br>R <sub>avg</sub> >96% @ 2000 - 10,000nm |
| <b>Coating:</b><br>Protected Gold (700-10000nm)                                                                  |
| <b>Coating Type:</b><br>Metal                                                                                    |
| <b>Clear Aperture CA (mm):</b><br>19.00 x 19.00                                                                  |
| <b>Edges:</b><br>Seamed, 0.5mm Maximum Edge Chip                                                                 |
| <b>Thickness (mm):</b><br>3.00                                                                                   |
| <b>Type:</b><br>Flat Mirror                                                                                      |
| <b>Wavelength Range (nm):</b><br>700 - 10000                                                                     |
| <b>Length (mm):</b><br>20.00                                                                                     |
| <b>Width (mm):</b><br>20.00                                                                                      |
| <b>Damage Threshold, By Design:</b> <input type="checkbox"/><br>0.8 J/cm² @ 1064nm, 10ns                         |

## Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 235:</b><br><a href="#">Compliant</a>             |