


TECHSPEC[®] 25.4mm Diameter x 350mm FL, 370-550nm Coated, Ultrafast Thin PCX Lens



Stock #11-682 ☐ In Stock

[Other Coating Options](#)



1



\$132.00

ADD TO CART

Qty 1-5

\$132.00

Qty 6+

\$116.00

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
25.40 +0.00/-0.10

Effective Focal Length EFL (mm):
350.41 @587.6nm

Back Focal Length BFL (mm):
349.31

Coating: BBAR (370-550nm)
Coating Specification: R_{abs} <0.55% @ 370 - 550nm
Substrate: ☐ Fused Silica (Corning 7980)
Surface Quality: 20-10
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/8
Focal Length Tolerance (%): ±1
Centering (arcmin): <3
Center Thickness CT (mm): 1.60 ±0.10
Edge Thickness ET (mm): 1.1
Radius R₁ (mm): 160.65
Clear Aperture CA (mm): 22.86
f/#: 13.78
Numerical Aperture NA: 0.037
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 370 - 550
Angle of Incidence (°): 0
Damage Threshold, By Design: ☐ 7.5 J/cm² @ 355nm, 20ns, 20Hz

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View