


NOTES:


1. SUBSTRATE: POLYMER FILM XP42-40
2. OPERATING TEMPERATURE: -40 to +80 °C
3. WAVELENGTH RANGE: 400 - 700nm
4. EXTINCTION RATIO: 9,000:1
5. POLARIZATION EFFICIENCY (%): > 99.98
6. TRANSMISSION (%):
 SINGLE: 42 ± 2
 PARALLEL: 36.4
 CROSSED: <0.004
7. ROHS COMPLIANT



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
 DIMENSIONS ARE FOR REFERENCE ONLY

EO® Edmund Optics®

**FOR INFORMATION ONLY:
 DO NOT MANUFACTURE
 PARTS TO THIS DRAWING**

THIRD ANGLE PROJECTION 		TITLE	600 x 450mm LINEAR POLARIZING FILM (XP42-40)	
ALL DIMS IN	mm	DWG NO	14343	SHEET 1 OF 1