

NOTES:



1. SUBSTRATE:  
N-BK7
2. CENTERING TOLERANCE (AT 587.6nm):  
BEAM DEVIATION (HALF ANGLE): <3 arcmin
3. COATING (APPLY ACROSS COATING APERTURE)  
S1: SWIR (900-1700nm)  
Ravg < 0.5% @ 900 - 1700nm @ ±30° AOI  
Rabs < 1% @ 900 - 1700nm @ ±30° AOI  
S2: SWIR (900-1700nm)  
Ravg < 0.5% @ 900 - 1700nm @ ±30° AOI  
Rabs < 1% @ 900 - 1700nm @ ±30° AOI

4. EDGES: FINE GROUND

5. ASPHERIC FIGURE ERROR: 0.75 μm RMS

6. ASPHERIC SURFACE DESCRIBED BY (REF. COEFFICIENT TABLE):

$$Z_{ASPH}(Y) = \frac{(\frac{1}{RADIUS}) * Y^2}{1 + \sqrt{1 - (1+k) * (\frac{1}{RADIUS})^2 * Y^2}} + D * Y^2 + E * Y^4 + F * Y^6 + G * Y^8 + H * Y^{10} + J * Y^{12} + L * Y^{14}$$



SECTION A-A

**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

COEFFICIENT TABLE 6.

COEFFICIENT	S1
SEMI-DIAMETER	6.250000E+00
(1/RADIUS)	7.82472613E-02
k	-6.920000E-01
D	0.000000E+00
E	7.352300E-06
F	8.146400E-09
G	0.000000E+00
H	0.000000E+00
J	0.000000E+00
L	0.000000E+00

	S1	S2					
SHAPE	CONVEX	PLANO	BFL @ 780nm: 22.35				
RADIUS	12.780	INFINITY					
SURFACE QUALITY	40-20	40-20	THIRD ANGLE PROJECTION				
CLEAR APERTURE	11.25mm	11.25mm	ALL DIMS IN		mm	TITLE	12.5mm Dia., 0.25 NA, 900-1700nm Coated, NIR Aspheric Lens
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	DWG NO		16292	SHEET 1 OF 1	

Edmund Optics®