

FOCAL LENGTH (EFL): $-9 \pm 0,09$
 BACK FOCAL LENGTH (BFL): $-10,21$

1 AR COATING: YAG-BBAR
 $R(\text{abs}) < 0.25\% @ 532\text{nm}$
 $R(\text{abs}) < 0.25\% @ 1064\text{nm}$
 $R(\text{avg}) < 1.0\% @ 500 - 1100\text{nm}$

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	$7,07 \pm 0,007 \text{ CV}$	GLASS N-SF11 785/258	R	$\infty \text{ PL}$
Øe	8,1		Øe	8,1
3/	$3 (0,5) \lambda = 632,8 \text{ nm}$		3/	$3 (0,5) \lambda = 632,8 \text{ nm}$
4/	-		4/	3,82'
5/	40 - 20 (MIL-PRF-13830B)		5/	40 - 20 (MIL-PRF-13830B)
6/	-		6/	-

PROTECTIVE CHAMFERS AS NEEDED


ROHS: COMPLIANT SCALE: NONE $\lambda = 587,6\text{nm}$

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

INDICATIONS IN ACCORDANCE WITH ISO 10110

FIRST ANGLE PROJECTION



ALL DIMS IN: mm



Edmund Optics®

TITLE LENS PCV 9 X -9 YAGBBAR TS

DWG NO 21306

SHEET SIZE A4

SHEET 1 OF 1