

**TECHSPEC® 25.0mm Diameter x 300.0mm FL, 1064nm V-Coat, PCX Lens**



633nm Laser Line Coated Plano-Convex (PCX) Lenses



Stock **#69-625** ☐ In Stock

[Other Coating Options](#)

⊖ 1 ⊕

**\$53.00**

ADD TO CART

|                               |
|-------------------------------|
| Qty 1-9                       |
| \$53.00                       |
| Qty 10+                       |
| \$47.75                       |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

Get Product Downloads



Diameter (mm):  
25.00 +0.0/-0.025

Effective Focal Length EFL (mm):

|                                                                                        |
|----------------------------------------------------------------------------------------|
| 300.00 @587.6nm                                                                        |
| <b>Back Focal Length BFL (mm):</b><br>298.02                                           |
| <b>Coating:</b><br>Laser V-Coat (1064nm)                                               |
| <b>Coating Specification:</b><br>R <sub>abs</sub> <0.25% @ 1064nm                      |
| <b>Substrate:</b> <input type="checkbox"/><br><a href="#">N-BK7</a>                    |
| <b>Surface Quality:</b><br>40-20                                                       |
| <b>Power (P-V) @ 632.8nm:</b><br>1.5λ                                                  |
| <b>Irregularity (P-V) @ 632.8nm:</b><br>λ/4                                            |
| <b>Focal Length Tolerance (%):</b><br>±1                                               |
| <b>Centering (arcmin):</b><br><1                                                       |
| <b>Center Thickness CT (mm):</b><br>3.00 ±0.10                                         |
| <b>Edge Thickness ET (mm):</b><br>2.50                                                 |
| <b>Radius R<sub>1</sub> (mm):</b><br>155.04                                            |
| <b>Clear Aperture CA (mm):</b><br>24                                                   |
| <b>f/#:</b><br>12.00                                                                   |
| <b>Numerical Aperture NA:</b><br>0.04                                                  |
| <b>Design Wavelength DWL (nm):</b><br>1064                                             |
| <b>Type:</b><br>Plano-Convex Lens                                                      |
| <b>Bevel:</b><br>Protective bevel as needed                                            |
| <b>Damage Threshold, By Design:</b> <input type="checkbox"/><br>5 J/cm² @ 1064nm, 10ns |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 235:</b><br><a href="#">Compliant</a>             |