

SPOT DIAGRAM

47646INK
 TUE DEC 16 2008 UNITS ARE μm .
 FIELD : :
 RMS RADIUS : 3.779
 SED RADIUS : 6.064
 SCALE BAR : 20


REFERENCE : CHIEF RAY

EDMUND OPTICS
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)

47646INK
 TUE DEC 16 2008
 MAXIMUM FOCAL SHIFT RANGE: 638.6694 μm
 DIFFRACTION LIMITED RANGE: 190.355 μm
 PUPIL ZONE: 0.0000

CHROMATIC FOCAL SHIFT

EDMUND OPTICS
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)



TRANSVERSE RAY FAN PLOT

47646INK
 TUE DEC 16 2008
 MAXIMUM SCALE: $\pm 50.000 \mu\text{m}$.
 0.486 0.588 0.656

SURFACE: IMAGE

EDMUND OPTICS
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)

47646INK
 TUE DEC 16 2008
 DATA FOR 0.4250 TO 0.6750 μm .
 SURFACE: IMAGE

POLYCHROMATIC DIFFRACTION MTF

EDMUND OPTICS
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)