



SURFACE: IMA
 IMA: 0.000 MM
SPOT DIAGRAM
 47651INK
 TUE DEC 16 2008 UNITS ARE μm .
 FIELD : :
 RMS RADIUS : 3.819
 SED RADIUS : 6.763
 SCALE BAR : 20
 REFERENCE : CHIEF RAY

EDMUND OPTICS
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)
 47651INK
 TUE DEC 16 2008
 MAXIMUM FOCAL SHIFT RANGE: 1557.9070 μm
 DIFFRACTION LIMITED RANGE: 940.007 μm
 PUPIL ZONE: 0.0000

EDMUND OPTICS
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)
CHROMATIC FOCAL SHIFT



47651INK
 TUE DEC 16 2008
 MAXIMUM SCALE: $\pm 50.000 \mu\text{m}$.
 0.486 0.588 0.656
 SURFACE: IMAGE

EDMUND OPTICS
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)
 47651INK
 TUE DEC 16 2008
 DATA FOR 0.4250 TO 0.6750 μm .
 SURFACE: IMAGE

EDMUND OPTICS
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)
POLYCHROMATIC DIFFRACTION MTF