



SURFACE: IMA
 IDA: 0.000 MM
SPOT DIAGRAM

47657INK
 TUE DEC 16 2008 UNITS ARE μm .
 FIELD : :
 RMS RADIUS : 1.559
 SED RADIUS : 3.354
 SCALE BAR : 10
 REFERENCE : CHIEF RAY

EDMUND OPTICS
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)

47657INK
 TUE DEC 16 2008
 MAXIMUM FOCAL SHIFT RANGE: 104.0502 μm
 DIFFRACTION LIMITED RANGE: 58.729 μm
 PUPIL ZONE: 0.0000

EDMUND OPTICS
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)



TRANSVERSE RAY FAN PLOT

47657INK
 TUE DEC 16 2008
 MAXIMUM SCALE: $\pm 20.000 \mu\text{m}$.
 0.486 0.588 0.656
 SURFACE: IMAGE

EDMUND OPTICS
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)

47657INK
 TUE DEC 16 2008
 DATA FOR 0.4250 TO 0.6750 μm .
 SURFACE: IMAGE

EDMUND OPTICS
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)