

SURFACE: INA
 IDA: 0.000 MM
SPOT DIAGRAM

47702INK
 TUE DEC 16 2008 UNITS ARE μm .
 FIELD : 1
 RMS RADIUS : 5.177
 SED RADIUS : 14.749
 SCALE BAR : 40



REFERENCE : CHIEF RAY

EDMUND OPTICS
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)

47702INK
 TUE DEC 16 2008
 MAXIMUM FOCAL SHIFT RANGE: 107.0115 μm
 DIFFRACTION LIMITED RANGE: 25.846 μm
 PUPIL ZONE: 0.0000

CHROMATIC FOCAL SHIFT

EDMUND OPTICS
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)



TRANSVERSE RAY FAN PLOT

47702INK
 TUE DEC 16 2008
 MAXIMUM SCALE: $\pm 50.000 \mu\text{m}$.
 0.486 0.588 0.656

SURFACE: IMAGE

EDMUND OPTICS
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)

47702INK
 TUE DEC 16 2008
 DATA FOR 0.4250 TO 0.6750 μm .
 SURFACE: IMAGE

POLYCHROMATIC DIFFRACTION MTF

EDMUND OPTICS
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)