

SURFACE: IMA
 IMA: 0.000 MM
SPOT DIAGRAM

49793INK
 TUE DEC 16 2008 UNITS ARE μm .
 FIELD : 1
 RMS RADIUS : 21.038
 GEO RADIUS : 57.983
 SCALE BAR : 200


REFERENCE : CHIEF RAY

EDMUND OPTICS
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)

49793INK
 TUE DEC 16 2008
 MAXIMUM FOCAL SHIFT RANGE: 429.0982 μm
 DIFFRACTION LIMITED RANGE: 14.714 μm
 PUPIL ZONE: 0.0000

CHROMATIC FOCAL SHIFT

EDMUND OPTICS
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)



49793INK
 TUE DEC 16 2008
 MAXIMUM SCALE: $\pm 500.000 \mu\text{m}$.
 0.486 0.588 0.656

SURFACE: IMAGE

TRANSVERSE RAY FAN PLOT

EDMUND OPTICS
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)

49793INK
 TUE DEC 16 2008
 DATA FOR 0.4000 TO 1.0000 μm .
 SURFACE: IMAGE

POLYCHROMATIC DIFFRACTION MTF

EDMUND OPTICS
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)