

# TECHSPEC® HIGH RESOLUTION FIXED FOCAL LENGTH LENS #85-869 • 35mm FL • f/1.8 PRIMARY WD: 400 – 2000mm

Our TECHSPEC® High Resolution 5 Megapixel Fixed Focal Length Lenses are available in multiple focal lengths and feature multiple versions to optimize for different working distance ranges. Perfect for use on high-end 5 megapixel sensors that require 145 lp/mm resolution, these lenses offer an attractive price-to-performance ratio. All lenses feature locking focus and iris rings and a front filter thread to allow the use of standard optical filters, for increased versatility.




<b>Focal Length:</b>	35mm
<b>Minimum Working Distance<sup>1</sup>:</b>	100mm
<b>Focus Range<sup>1</sup>:</b>	100mm - ∞
<b>Primary Working Distance Range:</b>	400 - 2000mm
<b>Length at Near Focus:</b>	44.46mm
<b>Length at Far Focus:</b>	39.0mm
<b>Filter Thread:</b>	M25.5 x 0.5
<b>Maximum Rear Protrusion:</b>	0.7mm
<b>Camera Mount:</b>	C-Mount

<b>Maximum Sensor Format:</b>	2/3"
<b>Aperture (f/#) (lockable):</b>	f/1.8 - f/16
<b>Magnification Range:</b>	0X - 0.33X
<b>Distortion<sup>2</sup>:</b>	<1%
<b>Object Space NA<sup>2</sup>:</b>	0.018
<b>Number of Elements (Groups):</b>	8 (5)
<b>AR Coating:</b>	425 - 675nm BBAR
<b>Weight:</b>	106g


Sensor Size	1/4"	1/3"	1/2.5"	1/2"	1/1.8"	2/3"	Sony 2/3"	1"
<b>Field of View<sup>3,4</sup></b>	10.9mm - 5.9°	14.6mm - 7.8°	17.3mm - 9.3°	19.5mm - 10.4°	21.9mm - 11.69°	26.84mm - 14.3°	25.75mm - 13.7°	N/A
<b>Field of View<sup>3,5</sup></b>	41.6 - 205.6mm	55.6 - 274.1mm	66.0 - 325.5mm	74.1 - 365.6mm	83.4 - 411.3mm	102.1 - 508.8mm	98.0 - 482.6mm	N/A

1. From front of housing 2. At 500mm W.D. 3. Horizontal FOV on standard 4:3 sensor format  
4. For focusing range: Min. W.D. - infinite conjugate angular FOV 5. For primary range

Specifications subject to change



**Figure 1:** Distortion at the maximum sensor format. Positive values correspond to pincushion distortion, negative values correspond to barrel distortion.




**Figure 2:** Relative illumination (center to corner)


In both plots, field points corresponding to the image circle of common sensor formats are included. Plots represent theoretical values from lens design software. Actual lens performance varies due to manufacturing tolerances.

**TECHSPEC® HIGH RESOLUTION  
FIXED FOCAL LENGTH LENS**  
#85-869 • 35mm FL • f/1.8  
PRIMARY WD: 400 – 2000mm

**MTF & DOF: f/2.8  
WD: 500mm**



**Figure 3:** Image space polychromatic diffraction FFT Modulation Transfer Function (MTF) for  $\lambda = 486\text{nm}$  to  $656\text{nm}$ . Included are Tangential and Sagittal values for field points on center, at 70% of full field and at the maximum sensor format. Solid black line indicates diffraction limit determined by  $f/\#$ -defined aperture. Frequencies corresponding to the Nyquist resolution limit of pixel sizes are indicated.




**Figure 4:** Polychromatic diffraction through-focus MTF at 20 linepairs/mm (image space). Contrast is plotted to two times the focus distance. Note object spatial frequency changes with working distance.


Plots represent theoretical values from lens design software. Actual lens performance varies due to manufacturing tolerances.

**TECHSPEC® HIGH RESOLUTION  
FIXED FOCAL LENGTH LENS**  
#85-869 • 35mm FL • f/1.8  
PRIMARY WD: 400 – 2000mm

**MTF & DOF: f/2.8  
WD: 2000mm**



**Figure 5:** Image space polychromatic diffraction FFT Modulation Transfer Function (MTF) for  $\lambda = 486\text{nm}$  to  $656\text{nm}$ . Included are Tangential and Sagittal values for field points on center, at 70% of full field and at the maximum sensor format. Solid black line indicates diffraction limit determined by  $f/\#$ -defined aperture. Frequencies corresponding to the Nyquist resolution limit of pixel sizes are indicated.




**Figure 6:** Polychromatic diffraction through-focus MTF at 20 linepairs/mm (image space). Contrast is plotted to two times the focus distance. Note object spatial frequency changes with working distance.


Plots represent theoretical values from lens design software. Actual lens performance varies due to manufacturing tolerances.

**TECHSPEC® HIGH RESOLUTION  
FIXED FOCAL LENGTH LENS**  
#85-869 • 35mm FL • f/1.8  
PRIMARY WD: 400 – 2000mm

**MTF & DOF: f/4.0  
WD: 500mm**



**Figure 7:** Image space polychromatic diffraction FFT Modulation Transfer Function (MTF) for  $\lambda = 486\text{nm}$  to  $656\text{nm}$ . Included are Tangential and Sagittal values for field points on center, at 70% of full field and at the maximum sensor format. Solid black line indicates diffraction limit determined by  $f/\#$ -defined aperture. Frequencies corresponding to the Nyquist resolution limit of pixel sizes are indicated.




**Figure 8:** Polychromatic diffraction through-focus MTF at 20 linepairs/mm (image space). Contrast is plotted to two times the focus distance. Note object spatial frequency changes with working distance.


Plots represent theoretical values from lens design software. Actual lens performance varies due to manufacturing tolerances.

**TECHSPEC® HIGH RESOLUTION  
FIXED FOCAL LENGTH LENS**  
#85-869 • 35mm FL • f/1.8  
PRIMARY WD: 400 – 2000mm

**MTF & DOF: f/4.0  
WD: 2000mm**



**Figure 9:** Image space polychromatic diffraction FFT Modulation Transfer Function (MTF) for  $\lambda = 486\text{nm}$  to  $656\text{nm}$ . Included are Tangential and Sagittal values for field points on center, at 70% of full field and at the maximum sensor format. Solid black line indicates diffraction limit determined by  $f/\#$ -defined aperture. Frequencies corresponding to the Nyquist resolution limit of pixel sizes are indicated.



**Figure 10:** Polychromatic diffraction through-focus MTF at 20 linepairs/mm (image space). Contrast is plotted to two times the focus distance. Note object spatial frequency changes with working distance.

Plots represent theoretical values from lens design software. Actual lens performance varies due to manufacturing tolerances.