




**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



LONGPASS FILTER

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

| REV. A | VALUE |
|------------------------------------|----------------------|
| SHAPE | PLANO |
| SPECTRAL TRANSMITTANCE $t_p(\%)$ | 93 |
| PASSBAND LIMIT λ_{p1} (nm) | 620 |
| CUT-OFF POSITION λ_c (nm) | 550±6 |
| STOPBAND LIMIT λ_s (nm) | 480 |
| WAVELENGTH | VIS |
| BEVEL | PROTECTIVE AS NEEDED |



| | | | |
|------------------------|-------|--|--------------|
| THIRD ANGLE PROJECTION | TITLE | 50.8 x 50.8mm, SCHOTT OG-550 LONGPASS FILTER | |
| ALL DIMS IN | mm | DWG NO | 32764 |
| | | | SHEET 1 OF 1 |