




**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



LONGPASS FILTER

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	VALUE
SHAPE	PLANO
SPECTRAL TRANSMITTANCE $t_{ig}(\%)$	97
PASSBAND LIMIT λ_{p1} (nm)	950
CUT-OFF POSITION λ_c (nm)	830±9
STOPBAND LIMIT λ_s (nm)	670
WAVELENGTH	IR
BEVEL	PROTECTIVE AS NEEDED



ALL DIMS IN

mm

TITLE

50.8 x 50.8mm, RG-830 LONGPASS FILTER

DWG NO

32768

SHEET
1 OF 1