



NOTES:

1. SUBSTRATE:  
N-BK7
2. COATING (APPLY ACROSS COATING APERTURE)  
S1: Protected Gold (700-10000nm)  
R(AVG) >96% @ 700 - 2000  
R(AVG) >96% @ 2000 - 10000nm  
S2: NONE

 FINE GRIND SURFACE



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

|                 | S1                   | S2                   |
|-----------------|----------------------|----------------------|
| SHAPE           | PLANO                | PLANO                |
| SURFACE QUALITY | 60-40                | 60-40                |
| CLEAR APERTURE  | $\lambda/4$          | $\lambda/4$          |
| BEVEL           | PROTECTIVE AS NEEDED | PROTECTIVE AS NEEDED |

THIRD ANGLE PROJECTION 

ALL DIMS IN

mm

 **Edmund Optics®**

TITLE

30mm Protected Gold Coated, N-BK7 Right Angle Mirror

DWG NO

47031

SHEET  
1 OF 1