NOTES:


1. WAVELENGTH RANGE:: 400 - 700nm


2. COATING: UNCOATED

FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

FINE GRIND SURFACE

4. ROHS COMPLIANT





SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

	\$1	\$2	
SHAPE	PLANO	-50 80-50	
SURFACE QUALITY	80-50		
SURFACE ACCURACY	COMMERCIAL POLISH		
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	

	THIRD ANGLE PROJECTION	$\phi \Box$	TITLE
)	ALL DIMS IN	mm	DWG NO

Eam	una	Opt	ICS <sup>®</sup>
100 - 100	VALUETE DU		N A C C

	TITLE	100 X 100MM WHILE DIT 03ING GLA	33
nm	DWG NO	34480	SHEET 1 OF 1