

NOTES:



1. SUBSTRATE MATERIAL:  
N-BK7

2. COATING (APPLY ACROSS CLEAR APERTURE)

S1 & S2: VIS 0° (425-675nm)  
R(AVG) ≤0.4% @ 425 - 675nm



△ 3. FINE GROUND SURFACE

4. RoHS COMPLIANT



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2	EFL	75.00	 <b>Edmund Optics®</b>	TITLE 50mm H X 25mm L X 75mm FL VIS 0° COATED, CYLINDER LENS	
SHAPE	CONVEX	PLANO	BFL	68.07			
RADIUS	38.89	INFINITY	THIRD ANGLE PROJECTION 		DWG NO	69736	SHEET 1 OF 1
SURFACE QUALITY	60-40	60-40					
CLEAR APERTURE	49.00 x 24.00	49.00 x 24.00	ALL DIMS IN	mm			
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED					