

NOTES:

1. SUBSTRATE MATERIAL:  
N-BK7




2. COATING (APPLY ACROSS CLEAR APERTURE)

S1 & S2: NONE

3. FINE GROUND SURFACE

4. POWER, IRREGULARITY, AND SURFACE QUALITY SPECIFICATIONS APPLY ACROSS CLEAR APERTURE

5. RoHS COMPLIANT



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	S1	S2	EFL	20		5mm H X 10mm L X 20mm FL UNCOATED, CYLINDER LENS	
SHAPE	CONVEX	PLANO	BFL	19.34			
RADIUS	10.32	$\infty$	THIRD ANGLE PROJECTION		TITLE		
SURFACE QUALITY	60-40	60-40	ALL DIMS IN	mm	DWG NO		
CLEAR APERTURE	9.00 X 4.00	9.00 X 4.00					SHEET 1 OF 1
COATING APERTURE	9.00 X 4.00	9.00 X 4.00					
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED					