



NOTES:

1. COATING (APPLY ACROSS CLEAR APERTURE)
LASER V-COAT
R(ABS) ≤ 0.25% @ 1064nm
2. RoHS: COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

DAMAGE THRESHOLD (PULSED)	10J/cm ² @ 10ns, 20Hz, 1064nm
DESIGN WAVELENGTH DWL (nm)	1064
EXPANSION POWER	10X
TRANSMISSION (%)	> 99 (NOMINAL)
NOMINAL PERFORMANCE	<λ/10 FOR 2.3mm INPUT BEAM (NOMINAL)



ALL DIMS IN mm



TITLE	10X 1064nm VEGA™ Nd:YAG LASER LINE BEAM EXPANDER	
DWG NO	35117	SHEET 1 OF 1