




NOTES:


1. SUBSTRATE: TAC Film
2. CONTRAST: >4, 250:1 (@ 550nm)
3. TRANSMISSION (%): 85 (Typical @ 550nm)
4. WAVELENGTH RANGE: 400 - 1200 nm
5. ORIENTATION OF AXIS:  $0^\circ \pm 1.5^\circ$   
NOTCHES ON POLARIZING FILM DEPICT DIRECTION OF POLARIZATION DIRECTION
6. RoHS NOT COMPLIANT



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

**EO<sup>®</sup> Edmund Optics<sup>®</sup>**

THIRD ANGLE PROJECTION 		TITLE	20.0 x 20.0mm, WIRE GRID POLARIZING FILM	
ALL DIMS IN	mm	DWG NO	34252	SHEET 1 OF 1