



NOTES:

1. WAVELENGTH RANGE: 400 - 700nm
2. COATING:
S1 & S2: NONE
3. FINE GRIND SURFACE
4. ROHS: COMPLIANT




**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY



REV. A.	S1	S2
SHAPE	PLANO	PLANO
SURFACE ACCURACY	COMMERCIAL POLISH	COMMERCIAL POLISH
SURFACE QUALITY	80-50	80-50
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED

THIRD ANGLE PROJECTION 

ALL DIMS IN mm

TITLE	DWG NO	SHEET
WHITE DIFFUSER GLASS, 15mm DIA	37975	1 OF 1