




NOTES:


1. SUBSTRATE: FLOAT GLASS
2. LINE PAIRS PER mm: 40lp/mm
3. COATING:  
S1 & S2:  
VACUUM DEPOSITED CHROME, OD > 3.0
4. RoHS: COMPLIANT



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

**EO**® Edmund Optics®

THIRD ANGLE PROJECTION 		TITLE	40 lp/mm, 1" x 3", Float Glass, Ronchi Ruling	
ALL DIMS IN	mm	DWG NO	38260	SHEET 1 OF 1