




NOTES:


1. SUBSTRATE: FLOAT GLASS
2. LINE PAIRS PER mm: 400lp/mm
3. COATING:  
S1 & S2:  
VACUUM DEPOSITED CHROME, OD > 3.0
4. RoHS: COMPLIANT



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

**EO<sup>®</sup> Edmund Optics<sup>®</sup>**

|  |    |        |  |                 |
|--|----|--------|--|-----------------|
| THIRD ANGLE PROJECTION  |    | TITLE  | 400 lp/mm, 1" x 3", Float Glass, Ronchi Ruling |                 |
| ALL DIMS IN  | mm | DWG NO | 57899  | SHEET<br>1 OF 1 |